## NOTES:


SUBSTRATE: FUSED SILICA


2. RoHS: COMPLIANT

3. SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN < 5 ARCMIN

4. COATING (APPLY ACROSS COATING APERTURE) \$1& \$2: R(ABS) ≤0.25% @ 880nm R(AVG) ≤1.25% FROM 400 - 870nm R(AVG) ≤1.25% FROM 890 - 1000nm







## FOR INFORMATION ONLY: PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2				Edmund Option	C®
SHAPE	PLANO	PLANO					
SURFACE ACCURACY	1λ	1λ		1		12.5 x 12.5mm VIS-NIR COATED, 1λ FUSE	D
SURFACE QUALITY	60-40	60-40	THIRD ANGLE PROJECTION		TITLE	SILICA WINDOW	
CLEAR APERTURE	11.25 x 11.25	11.25 x 11.25					
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	49640	SHEET 1 OF 1

