



TECHSPEC® Achromatic Lenses

Edmund Optics Inc.



USA | UK | France | Germany | Japan | Singapore | China | Korea | Italy

TECHSPEC® ACHROMATIC LENSES



SURFACE: 10A		DPA: 0.000 MM	
SPOT DIAGRAM			
47663INK		EDMUND OPTICS	
TUE DEC 16 2008		HTTP://WWW.EDMUNDOPTICS.COM	
UNITS ARE μm .			
FIELD :			
RMS RADIUS :			
GE0 RADIUS :			
SCALE BAR :			
100		REFERENCE : CHIEF RAY	

CHROMATIC FOCAL SHIFT		EDMUND OPTICS	
47663INK		HTTP://WWW.EDMUNDOPTICS.COM	
TUE DEC 16 2008			
MAXIMUM FOCAL SHIFT RANGE: 75.7268 μm			
DIFFRACTION LIMITED RANGE: 13.200 μm			
PUPIL ZONE: 0.0000			



Edmund
optics | worldwide

www.edmundoptics.com