



NOTES:

1. ALLOWABLE OPTICAL MATERIAL: GRADE A FINE ANNEALED SCHOTT: N-BK7
2. SURFACE S2 TO BE PARALLEL WITH SURFACE S1 TO WITHIN 5 ARCMIN
3. COATING (APPLY ACROSS COATING APERTURE)  
S1: NONE  
S2: NONE

4. SIX SIDEWALLS:  
SURFACE ACCURACY: COMMERCIAL POLISH



**FOR INFORMATION ONLY:**  
**DO NOT MANUFACTURE PARTS TO THIS DRAWING**



	S1	S2			TITLE	12.5mm HEX LIGHT PIPE, 250mm lg
SHAPE	PLANO	PLANO	EFL (AT 587.6nm)	NA	DWG NO	84531
SURFACE ACCURACY AT 632.8nm	3 WAVES	3 WAVES	BFL (AT 587.6nm)	NA		
SURFACE QUALITY	60 - 40	60 - 40	ALL DIMS IN	mm		