




NOTES:

1. SUBSTRATE  
BOROFLOAT®
2. COATING PERFORMANCE (APPLY ACROSS COATING APERTURE)  
T(AVG) <1.0% @ 400 - 475nm  
T(AVG) >80% @ 550 - 750nm
3. CUT AND SEAM
4. ROHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	80-50	80-50
CLEAR APERTURE	≥85 %	≥85 %
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION

ALL DIMS IN

mm

Edmund Optics®

TITLE

50 x 50 YELLOW DICHROIC FILTER

DWG NO

30637

SHEET  
1 OF 1