




NOTES:

- 1. SUBSTRATE:  
BOROFLOAT®
- 2. COATING PERFORMANCE (APPLY ACROSS COATING APERTURE)  
T(AVG) <1.0% @ 535 - 565nm  
T(AVG) <80% @ 380 - 470nm  
T(AVG) >80% @ 655 - 750nm

3. FINE GROUND SURFACE

- 4. ROHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	80-50	80-50
CLEAR APERTURE	≥85%	≥85%
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE  
PROJECTION

ALL DIMS IN      mm

**EO**® **Edmund Optics®**

TITLE	50mm Diameter, Magenta Dichroic Filter
DWG NO	52541
SHEET	1 OF 1