




**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



BANDPASS FILTER

REV A	VALUE
CENTER WAVELENGTH (CWL)	1064 ± 2nm
FULL WIDTH HALF MAX (FWHM)	7.5± 2nm
MINIMUM TRANSMISSION	≥90 %
BLOCKING	979 - 1048 & 1080 - 1170
SURFACE QUALITY	60-40
COATING TYPE	HARD COATED
DURABILITY	DURABILITY: MIL-C-48497A SECT. 3.4.1
ENVIRONMENTAL	ENVIRONMENTAL: MIL-STD-810F SECT. 507.4

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**EO**® **Edmund Optics**®

THIRD ANGLE PROJECTION		TITLE	OD6, Ø25mm, 1064 nm CWL, 4 nm BANDWIDTH, LASER LINE BANDPASS FILTER
ALL DIMS IN	mm	DWG NO	68985
			SHEET 1 OF 1