





**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



BANDPASS FILTER

	VALUE
OPTICAL DENSITY	$\geq 3.0$
CENTER WAVELENGTH (CWL)	$650 \pm 15 \text{ nm}$
FULL WIDTH HALF MAX (FWHM)	$80 \pm 25 \text{ nm}$
MINIMUM TRANSMISSION	$\geq 60 \%$
BLOCKING	200 - 1200nm
SURFACE QUALITY	80-50
CONSTRUCTION	MOUNTED IN BLACK ANODIZED RING
COATING TYPE	TRADITIONAL COATED

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY



ALL DIMS IN

mm

TITLE

Ø25mm, 650nm x 80nm, MOUNTED  
BANDPASS FILTER

DWG NO

65746

SHEET  
1 OF 1