



NOTES:

1. SUBSTRATE:
BOROFLOAT®
2. COATING SPECIFICATION:
S1: Enhanced Aluminum (250-700nm)
R(AVG) >89% @ 250 - 450nm
R(AVG) >85% @ 250 - 700nm


3. FINE GROUND SURFACE

4. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

| | | | | | | | | |
|-----------------|----------------------|----------------------|---|----|--------|-------|---|--|
| | S1 | S2 |  | | | |  | |
| SHAPE | PLANO | PLANO | | | | | TITLE | 5 x 5mm UV Enhanced Aluminum, λ/4 Mirror |
| SURFACE QUALITY | 60-40 | COMMERCIAL POLISH | ALL DIMS IN | mm | DWG NO | 48408 | SHEET | 1 OF 1 |
| CLEAR APERTURE | 4.15 x 4.15 | N/A | | | | | | |
| BEVEL | PROTECTIVE AS NEEDED | PROTECTIVE AS NEEDED | | | | | | |