



NOTES:

1. SUBSTRATE:
BOROFLOAT®
2. COATING SPECIFICATION:
S1: Protected Silver (450-10000nm)
R(AVG) >98% @ 450 - 2000nm
R(AVG) >98% @ 2000 - 10,000nm


3. FINE GROUND SURFACE

4. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2				
SHAPE	PLANO	PLANO				
SURFACE QUALITY	60-40	COMMERCIAL POLISH	THIRD ANGLE PROJECTION		TITLE	40 x 40mm Protected Silver, λ/4 Mirror
CLEAR APERTURE	34.00 x 34.00	N/A	ALL DIMS IN	mm	DWG NO	88540
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	SHEET 1 OF 1			