



NOTES:

1. SUBSTRATE:
BOROFLOAT®
2. COATING SPECIFICATION:
S1: Enhanced Aluminum (250-700nm)
R(AVG) >89% @ 250 - 450nm
R(AVG) >85% @ 250 - 700nm

△ 3. FINE GROUND SURFACE


4. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY



	S1	S2					Edmund Optics® 25 x 25mm UV Enhanced Aluminum, λ/4 Mirror	
SHAPE	PLANO	PLANO						
SURFACE QUALITY	60-40	COMMERCIAL POLISH	ALL DIMS IN	mm	DWG NO	45334	SHEET	1 OF 1
CLEAR APERTURE	21.25 x 21.25	N/A						
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED						