

NOTES:




1. SUBSTRATE MATERIAL:
NITROCELLULOSE

2. COATING (APPLY ACROSS COATING APERTURE)

S1: METAL/DIELECTRIC
40% R @ 400 - 700nm @ 45° AOI
40% T @ 400 - 700nm @ 45° AOI
R/T TOLERANCE: ±3%

S2: NONE

3. ROHS : EXEMPT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV.A.	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	40-20	40-20
CLEAR APERTURE	Ø101.60	Ø101.60
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED



ALL DIMS IN

mm

EO® **Edmund Optics**®

TITLE

BS PELLICLE 4in DIA 40R/40T

DWG NO

39491

SHEET
1 OF 1