




NOTES:
1. RoHS: COMPLIANT

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



	VALUE
BEAM DIVERGENCE (mrad)	<1.00
COLOR	BLUE
OUTPUT POWER (mW)	50.00
POINTING STABILITY AFTER WARM UP (mrad/°C)	<0.05
POLARIZATION	>50:1
POWER STABILITY (%)	<2% RMS OVER 4 HOURS
WAVELENGTH (nm)	488
MODE QUALITY, M2	<1.50
MODULATION FREQUENCY (kHz)	1-10
BEAM DIAMETER (mm)	3.50

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

Edmund Optics®

THIRD ANGLE PROJECTION		TITLE	488nm 50mW LOW COST TURNKEY LASER	
ALL DIMS IN	mm	DWG NO	37091	SHEET 1 OF 1