


LEFT SURFACE			MATERIAL		RIGHT SURFACE		
R	92,083±0,092 CV		GLASS	FUSED SILICA 458/678	R	92,083±0,092 CV	
Øe	24				Øe	24	
3/	3 (0,5) λ=632,8 nm				3/	3 (0,5) λ=632,8 nm	
4/	-				4/	2,18'	
5/	40 - 20 (MIL-PRF-13830B)				5/	40 - 20 (MIL-PRF-13830B)	
6/	-				6/	-	
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	 Edmund Optics®			
ROHS: COMPLIANT		SCALE: NONE					
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE		25mm Dia, x -100mm FL, Uncoated, UV DCV Lens	
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING				DWG NO		48328	SHEET SIZE A4
INDICATIONS IN ACCORDANCE WITH ISO 10110				ALL DIMS IN:		mm	SHEET 1 OF 1