


NOTES:

- 1. SUBSTRATE: SCHOTT OG515
- 2. SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN 1 ARCMIN

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
SHAPE	PLANO
CUT-ON WAVELENGTH (nm)	515 ±6
PASSBAND LIMIT 1 (nm)	580
STOPBAND LIMIT (nm)	440
SURFACE QUALITY	60-40
CLEAR APERTURE	48.50 x 48.50
BEVEL MAX FACE	PROTECTIVE AS NEEDED

THIRD ANGLE  
PROJECTION

ALL DIMS IN      mm

 <b>Edmund Optics®</b>			
TITLE		SCHOTT OG515 50 x 50mm COLORED LONGPASS FILTER, 3mm THK	
DWG NO		14495	SHEET 1 OF 1