


NOTES:

- 1. SUBSTRATE: SCHOTT RG630
- 2. SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN 1 ARCMIN

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



	VALUE
SHAPE	PLANO
CUT-ON WAVELENGTH (nm)	630 ±6
PASSBAND LIMIT 1 (nm)	710
STOPBAND LIMIT (nm)	540
SURFACE QUALITY	60-40
CLEAR APERTURE	48.50 x 48.50
BEVEL MAX FACE	PROTECTIVE AS NEEDED

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY



THIRD ANGLE PROJECTION		TITLE	SCHOTT RG630 50 x 50mm COLORED LONGPASS FILTER, 2mm THK	
ALL DIMS IN	mm	DWG NO	14515	SHEET 1 OF 1