





- NOTES:
1. SUBSTRATE: UV FUSED SILICA
 2. ROHS: COMPLIANT

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



	VALUE
SHAPE	PLANO
SURFACE QUALITY	80-50
CENTER WAVELENGTH (nm)	289
FULL WIDTH HALF MAX (FWHM) (nm)	10±2
MIN TRANSMISSION (%)	15
CLEAR APERTURE	Ø45.00
BEVEL	PROTECTIVE AS NEEDED

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

 **Edmund Optics®**

THIRD ANGLE PROJECTION 	TITLE	289nm, 10nm FWHM, 50mm DIA. FIRST SURFACE UV BANDPASS FILTER		
	DWG NO	14925	SHEET 1 OF 1	