

## NOTES:

- 1. SUBSTRATE: N-BK7
- 2. S2 TO BE PARALLEL WITH S1 TO < 1ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE) \$1 & \$2: R(ABS) ≤0.25% @ 880nm R(AVG) ≤1.25% @ 400 - 870nm R(AVG) ≤1.25% @ 890 - 1000nm



5. Rohs Compliant





## FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2
SHAPE	PLANO	PLANO
SURFACE QUALITY	60-40	60-40
CLEAR APERTURE (mm)	Ø22.86	Ø22.86
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION	<b>\rightarrow</b>	TI
ALL DIMS IN	mm	D١

B	Edmund Optics®
TITLE	25.4mm DIA., 4mm THICK, VIS-NIR COATED λ/4 N-BK7 WINDOW

ALL DIMS IN	mm	DWG NO	15437	SHE 1 O
-------------	----	--------	-------	------------