



NOTES:


1. SUBSTRATE: ISUZU ISK153  
 DENSITY: 2.59g/cm<sup>3</sup>  
 REFLECTION FACTOR: 0.92  
 KNOOP HARDNESS: 481kg/mm<sup>2</sup>  
 REFRACTIVE INDEX: 1.522nm
  
2. SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN 3 ARCMIN

**FOR INFORMATION ONLY:  
 DO NOT MANUFACTURE  
 PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
 DIMENSIONS ARE FOR REFERENCE ONLY

	S1
SHAPE	PLANO
FUNCTION	HEAT ABSORBING
SURFACE QUALITY	60-40
CLEAR APERTURE	Ø22.50
BEVEL MAX FACE	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION 

ALL DIMS IN mm

 **Edmund Optics®**

TITLE	ISUZU ISK153, 25 Dia., HEAT ABSORBING COLORED GLASS FILTER	
DWG NO	15704	SHEET 1 OF 1