



NOTES:

1. SUBSTRATE: ISUZU ISK167
 DENSITY: 2.62g/cm³
 REFLECTION FACTOR: 0.92
 KNOOP HARDNESS: 502kg/mm²
 REFRACTIVE INDEX: 1.52nm
2. SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN 3 ARCMIN

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1
SHAPE	PLANO
FUNCTION	HEAT ABSORBING
SURFACE QUALITY	60-40
CLEAR APERTURE	$\varnothing 22.50$
BEVEL MAX FACE	PROTECTIVE AS NEEDED



ALL DIMS IN mm

EO® **Edmund Optics**®

TITLE

ISUZU ISK167, 25 Dia., HEAT ABSORBING
COLORED GLASS FILTER

DWG NO

15707

SHEET
1 OF 1