

NOTES:

1. SUBSTRATE:  
SCHOTT NG11

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**





2. FINE GRIND SURFACE

3. COATING SPECIFICATION:  
S1 & S2:NONE

4. OPTICAL DENSITY: 0.2


5. TRANSMISSION (%): 63.1

- ## 6. ROHS COMPLIANT



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY



	S1	S2	<div>THIRD ANGLE PROJECTION</div> 		TITLE	SCHOTT NG11, 0.2 OD, 25mm DIA., ABSORPTIVE ND FILTER	
SHAPE	PLANO	PLANO					
SURFACE QUALITY	80-50	80-50					
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	16721	SHEET 1 OF 1