

NOTES:

1. SUBSTRATE: BOROFLOAT33
2. COATING

DURABILITY:

PHYSICAL: MIL-C-48497A, SECTION 3.4.1

ENVIRONMENTAL: MIL-STD-810F, SECTION 507.4

PERFORMANCE SPECIFICATIONS @ 0° AOI




T(AVG): ≥85% FROM 400 - 580nm

T(AVG): ≤1% FROM 625 - 775nm

CUT-OFF WAVELENGTH: T(ABS) = 50% @ 600nm ± 12nm



3. ROHS COMPLIANT

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



SHORTPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2				
SHAPE	PLANO	PLANO	THIRD ANGLE PROJECTION 	TITLE	FILTER OD2 SHORTPASS 600nm 6mm x 6mm	
SURFACE QUALITY	60-40	60-40		DWG NO	15237	SHEET 1 OF 1
CLEAR APERTURE	5.40 x 5.40	5.40 x 5.40				
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED		ALL DIMS IN	mm	