




NOTES:

1. SUBSTRATE:  
AGC DRAGONTRAIL™
2. COATING (APPLY ACROSS CLEAR APERTURE)  
  
S1&S2: UNCOATED
3. FINE GRIND SURFACE
4. ROHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	80-50	80-50
CLEAR APERTURE (mm)	22.5	22.5
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED



ALL DIMS IN

mm

**EO**® **Edmund Optics**®

25mm Dia., 1.1mm Thick, Uncoated,  
Dragontrail™ Chemically Strengthened  
Window

TITLE

DWG NO

17257

SHEET  
1 OF 1