






**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**







SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
COLOR	Orange
OUTPUT POWER (mW)	200
POWER STABILITY (%)	<2% RMS over 4 hours
WAVELENGTH (nm)	589
MODULATION FREQUENCY (kHz)	1
FIBER LENGTH (m)	1.0



Edmund Optics®			
TITLE	200mW, 589nm LC Turnkey Laser Fiber SMA		
DWG NO	19506	SHEET 1 OF 1	



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

Edmund Optics®

THIRD ANGLE PROJECTION		TITLE	Laser LC Turnkey 589nm x 200mW Fiber SMA	
ALL DIMS IN	mm	DWG NO	19506	SHEET 1 OF 1