



NOTES:

- 1. SUBSTRATE:
AS87ECO
- 2. COATING (APPLY ACROSS CLEAR APERTURE)

S1 & S2: NONE

- 3. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	80-50	80-50
SURFACE ROUGHNESS	< 0.50nm	< 0.50nm
CLEAR APERTURE	Ø 9.00	Ø 9.00
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

THIRD ANGLE PROJECTION

ALL DIMS IN mm

EO® Edmund Optics®

TITLE

SCHOTT AS87ECO, 10mm Dia., 0.1mm Thick,
Ultra-Thin Window

DWG NO

20208

SHEET
1 OF 1