




NOTES:


1. SUBSTRATE: BOROFLOAT®
2. COATING (APPLY ACROSS CLEAR APERTURE):
S1 & S2: NONE
3.  FINE GRIND SURFACE
4. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE FLATNESS	4 - 6λ	4 - 6λ
SURFACE QUALITY	80 - 50	80 - 50
CLEAR APERTURE	∅ 90.00	∅ 90.00
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION 

ALL DIMS IN mm

 **Edmund Optics®**

TITLE

100mm Diameter x 3.3mm Thickness,
Uncoated, BOROFLOAT® Window

DWG NO

29395

SHEET
1 OF 1