NOTES:
1. RoHS: EXEMPT

FOR INFORMATION ONLY:
DO NOT MANUFACTURE PARTS TO THIS DRAWING



	VALUE
WEIGHT (lbs)	1.2
WARM-UP TIME	10
RMS NOISE	30 Hz - 10 MHz: 1.0%
INPUT VOLTAGE (V)	220
OPERATING LIFETIME (HOURS)	12,000
MINIMUM OUTPUT POWER, TEM00 (mW)	0.5
LONGITUDINAL MODE SPACING, NOMINAL (MHz)	1090
LASER CLASS - CDRH	II
COLOR	RED
OUTPUT POWER (mW)	0.5
BEAM DIAMETER (mm)	0.48 ± 3
BEAM DIVERGENCE (mrad)	1.7
POLARIZATION	500:1

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

Edmund Optics®

THIRD ANGLE PROJECTION		TITLE	0.5mW 220V Linear, HeNe Laser	
ALL DIMS IN	in	DWG NO	61360	SHEET 1 OF 1