



NOTES:

- 1. ALLOWABLE OPTICAL MATERIAL: GRADE A FINE ANNEALED SCHOTT: Borofloat®
- 2. COATING (APPLY ACROSS CLEAR APERTURE)
S1: MULTILAYER DIELECTRIC FOR 0° AOI
T(AVG) ≥ 85% FROM 425-675nm
R(AVG) ≥ 90% FROM 750-1150nm
R(AVG) ≥ 80% FROM 1200-1600nm

S2: NONE
3. EDGES: SEAMED



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY
DIMENSIONS ARE IN mm [INCHES]

	S1	S2	EFL (AT 587.6nm)	NA	 Edmund Optics®	
SHAPE	PLANO	PLANO				
SURFACE ACCURACY AT 632.8nm	4-6 WAVES PER INCH	4-6 WAVES PER INCH			TITLE EXTENDED HOT MIRROR 101x127mm	
SURFACE QUALITY	80 - 50	80 - 50	BFL (AT 587.6nm)	NA		
CLEAR APERTURE	≥ 85.85 x 107.95	≥ 85.85 x 107.95			DWG NO 47304	
BEVEL MAX FACE	0.5 x 45°	0.5 x 45°	ALL DIMS IN	mm		