





+ 0.1861
x 0.5876
■ 0.6563



SURFACE: INA

DIA: 0.000 MM

SPOT DIAGRAM

63710
MON APR 27 2009 UNITS ARE μm.
FIELD : 1
RMS RADIUS : 2.059
CED RADIUS : 4.853
SCALE BAR : 10


REFERENCE : CHIEF RAY

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

CHROMATIC FOCAL SHIFT

63710
MON APR 27 2009
MAXIMUM FOCAL SHIFT RANGE: 164.9568 μm
DIFFRACTION LIMITED RANGE: 72.225 μm
PUPIL ZONE: 0.0000

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM




OBJ: 0.0000 DEG

TRANSVERSE RAY FAN PLOT

63710
MON APR 27 2009
MAXIMUM SCALE: ± 50.000 μm.
0.486 0.588 0.656

SURFACE: IMAGE

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM



TS DIFF. LIMIT
TS 0.0000 DEG

POLYCHROMATIC DIFFRACTION MTF

63710
MON APR 27 2009
DATA FOR 0.4250 TO 0.6750 μm.
SURFACE: IMAGE

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM