

TECHSPEC® UC SERIES FIXED FOCAL LENGTH LENSES

#33-303 • 12mm FL • f/1.8

Our ultra-compact, TECHSPEC® UC Series Fixed Focal Length Lenses are designed to optimize performance, cost, and size without sacrificing quality or feel. Designed for pixels that are $\leq 2.2\mu\text{m}$, these lenses provide high levels of resolution ($>200\text{ lp/mm}$) across the sensor and are compatible with all standard C-Mount cameras. TECHSPEC® UC Series Fixed Focal Length Lenses feature focus and iris adjustments, as well as recessed set screws, and are manufactured for use at typical machine vision working distances. While they are optimized for $1/2.5"$ sensors, many focal lengths will work on sensors up to $1/1.8"$. The TECHSPEC® UC Series lenses are an outstanding option for use on all smaller format camera sensors, along with both short and long working distance applications, making them ideal for inspection, factory automation, biomedical devices, and a broad range of other applications.



TECHSPEC® UC SERIES FIXED FOCAL LENGTH LENSES

Focal Length:	12mm
Minimum Working Distance¹:	100mm
Focus Range:	100mm - ∞
Length at Near Focus:	32.48mm
Length at Far Focus:	35.2mm
Filter Thread:	M25.5 x 0.5
Max. Sensor Format:	$1/1.8"$
Optimized Sensor Format:	$1/2.5"$

Camera Mount:	C-Mount
Aperture (f/#):	f/1.8 - f/11
Magnification Range:	0X - 0.106X
Distortion:	<2.5% (on $1/2.5"$ sensor)
Object Space NA:	0.029
Number of Elements (Groups):	7 (6)
AR Coating:	$1/4\lambda$ MgF ₂
Weight:	49g

Sensor Size	$1/4"$	$1/3"$	$1/2.5"$	$1/2"$	$1/1.8"$	$2/3"$	$1"$	$4/3"$
Field of View²	34mm - 16.8°	45.3mm - 22.3°	53.2mm - 26°	60.2mm - 29.2°	68mm - 32.8°	NA	NA	NA

1. From front of housing 2. Horizontal FOV on standard 4:3 sensor format. Min. W.D. - angular FOV at infinite conjugate Specifications subject to change




Figure 1: Distortion at the maximum sensor format. Positive values correspond to pincushion distortion, negative values correspond to barrel distortion.




Figure 2: Relative illumination (center to corner)

In both plots, field points corresponding to the image circle of common sensor formats are included. Plots represent theoretical values from lens design software. Actual lens performance varies due to manufacturing tolerances.

TECHSPEC® UC SERIES FIXED FOCAL LENGTH LENSES
#33-303 • 12mm FL • f/1.8

MTF & DOF: f/1.8
WD: 200mm




Figure 3: Image space polychromatic diffraction FFT Modulation Transfer Function (MTF) for $\lambda = 486\text{nm}$ to 656nm . Included are Tangential and Sagittal values for field points on center, at 70% of full field and at the maximum sensor format. Solid black line indicates diffraction limit determined by $f/\#$ -defined aperture. Frequencies corresponding to the Nyquist resolution limit of pixel sizes are indicated.




Figure 4: Polychromatic diffraction through-focus MTF at 20 linepairs/mm (image space). Contrast is plotted to two times the focus distance. Note object spatial frequency changes with working distance.

Plots represent theoretical values from lens design software. Actual lens performance varies due to manufacturing tolerances.

TECHSPEC® UC SERIES FIXED FOCAL LENGTH LENSES
#33-303 • 12mm FL • f/1.8

MTF & DOF: f/1.8
WD: 350mm

TECHSPEC® UC SERIES FIXED FOCAL LENGTH LENSES




Figure 5: Image space polychromatic diffraction FFT Modulation Transfer Function (MTF) for $\lambda = 486\text{nm}$ to 656nm . Included are Tangential and Sagittal values for field points on center, at 70% of full field and at the maximum sensor format. Solid black line indicates diffraction limit determined by $f/\#$ -defined aperture. Frequencies corresponding to the Nyquist resolution limit of pixel sizes are indicated.




Figure 6: Polychromatic diffraction through-focus MTF at 20 linepairs/mm (image space). Contrast is plotted to two times the focus distance. Note object spatial frequency changes with working distance.

Plots represent theoretical values from lens design software. Actual lens performance varies due to manufacturing tolerances.

TECHSPEC® UC SERIES FIXED FOCAL LENGTH LENSES
#33-303 • 12mm FL • f/1.8

MTF & DOF: f/4.0
WD: 200mm




Figure 7: Image space polychromatic diffraction FFT Modulation Transfer Function (MTF) for $\lambda = 486\text{nm}$ to 656nm . Included are Tangential and Sagittal values for field points on center, at 70% of full field and at the maximum sensor format. Solid black line indicates diffraction limit determined by $f/\#$ -defined aperture. Frequencies corresponding to the Nyquist resolution limit of pixel sizes are indicated.




Figure 8: Polychromatic diffraction through-focus MTF at 20 linepairs/mm (image space). Contrast is plotted to two times the focus distance. Note object spatial frequency changes with working distance.

Plots represent theoretical values from lens design software. Actual lens performance varies due to manufacturing tolerances.

TECHSPEC® UC SERIES FIXED FOCAL LENGTH LENSES
#33-303 • 12mm FL • f/1.8

MTF & DOF: f/4.0
WD: 350mm




Figure 9: Image space polychromatic diffraction FFT Modulation Transfer Function (MTF) for $\lambda = 486\text{nm}$ to 656nm . Included are Tangential and Sagittal values for field points on center, at 70% of full field and at the maximum sensor format. Solid black line indicates diffraction limit determined by $f/\#$ -defined aperture. Frequencies corresponding to the Nyquist resolution limit of pixel sizes are indicated.




Figure 10: Polychromatic diffraction through-focus MTF at 20 linepairs/mm (image space). Contrast is plotted to two times the focus distance. Note object spatial frequency changes with working distance.

Plots represent theoretical values from lens design software. Actual lens performance varies due to manufacturing tolerances.