



NOTES:

1. SUBSTRATE:
Schott KG-3
2. COATING (APPLY ACROSS COATING APERTURE)
S1 & S2: NONE



 FINE GRIND SURFACE


4. WAVELENGTH RANGE: 300 - 2700 nm
5. DENSITY (g/cm³): 2.53
OPERATING TEMPERATURE (°C): 300 Maximum
REFLECTION FACTOR: 0.92
6. ROHS: COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

 **Edmund Optics®**

| | | | | | | | |
|-----------------|---------------------|---------------------|--|----|--------|--|-------|
| | S1 | S2 | THIRD ANGLE PROJECTION  | | TITLE | 12.5mm Dia. SCHOTT KG-3 Heat Absorbing Glass | |
| SHAPE | PLANO | PLANO | | | DWG NO | 49087 | SHEET |
| SURFACE QUALITY | 60-40 | 60-40 | ALL DIMS IN | mm | | | |
| BEVEL | PROTECTED AS NEEDED | PROTECTED AS NEEDED | | | | | |