




**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



BANDPASS FILTER

REV A	VALUE
CENTER WAVELENGTH (CWL)	785 ± 2nm
FULL WIDTH HALF MAX (FWHM)	5.5± 2nm
MINIMUM TRANSMISSION	≥90 %
BLOCKING	722 - 773 & 797 - 864
SURFACE QUALITY	60-40
CONSTRUCTION	MOUNTED IN BLACK ANODIZED ALUMINUM RING
COATING TYPE	HARD COATED
DURABILITY	DURABILITY: MIL-C-48497A SECT. 3.4.1
ENVIRONMENTAL	ENVIRONMENTAL: MIL-STD-810F SECT. 507.4

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY



ALL DIMS IN mm

TITLE OD6, Ø12.5mm, 785 nm CWL, 3 nm BANDWIDTH, LASER LINE BANDPASS FILTER

DWG NO 68947

SHEET 1 OF 1