



NOTES:

- 1. SUBSTRATE:
Schott KG-3
- 2. COATING (APPLY ACROSS COATING APERTURE)
S1 & S2: NONE
- 3. FINE GRIND SURFACE
- 4. WAVELENGTH RANGE: 300 - 2700 nm
- 5. DENSITY (g/cm3): 2.53
OPERATING TEMPERATURE (°C): 300 Maximum
REFLECTION FACTOR: 0.92
- 6. ROHS: COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY



	S1	S2	THIRD ANGLE PROJECTION		TITLE	25mm Dia. SCHOTT KG-3 Heat Absorbing Glass	
SHAPE	PLANO	PLANO					
SURFACE QUALITY	60-40	60-40	ALL DIMS IN	mm	DWG NO	49088	SHEET 1 OF 1
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED					