


NOTES:

- 1. SUBSTRATE:
FUSED SILICA MOUNTED IN BLACK ANODIZED ALUMINUM RING
- 2. TRANSMITTED WAVEFRONT ERROR: $\lambda/4$
- 3. RoHS: COMPLIANT

FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING



	VALUE
CENTER WAVELENGTH (CWL) (nm)	832 ± 4
MINIMUM BANDWIDTH (nm)	37
FULL WIDTH HALF MAX (FWHM) (nm)	45
MINIMUM TRANSMISSION (%)	>93
OD6 BLOCKING RANGE (nm)	550 - 794 & 878 - 1075
SURFACE QUALITY	60-40
COATING TYPE	HARD COATED
DURABILITY	MIL-C-48497A, SECT. 3.4.1
ENVIRONMENTAL	MIL-STD-801F, SECT. 507.4

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

Edmund Optics®



ALL DIMS IN

mm

TITLE

OD6, Ø25mm, 832nm x 45nm, BP
FLUORESCENCE FILTER

DWG NO

84107

SHEET
1 OF 1