



NOTES:

1. SUBSTRATE:
FUSED SILICA MOUNTED IN BLACK ANODIZED ALUMINUM RING
2. TRANSMITTED WAVEFRONT ERROR: $\lambda/4$
3. RoHS: COMPLIANT


**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



	VALUE
CENTER WAVELENGTH (CWL) (nm)	452 $\pm$ 3
MINIMUM BANDPATH (nm)	45
FULL WIDTH HALF MAX (FWHM) (nm)	51
MINIMUM TRANSMISSION (%)	>93
OD6 BLOCKING RANGE (nm)	370 - 410
SURFACE QUALITY	60-40
COATING TYPE	HARD COATED
DURABILITY	MIL-C-48497A, SECT. 3.4.1
ENVIRONMENTAL	MIL-STD-801F, SECT. 507 .4

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

 **Edmund Optics®**

THIRD ANGLE
PROJECTION 

ALL DIMS IN

mm

TITLE

OD6, $\phi 12.5$ mm, 452nm x 45nm, BP
FLUORESCENCE FILTER

DWG NO

86340

SHEET
1 OF 1