


NOTES:

1. SUBSTRATE
2. SURFACE S2 TO BE PARALLEL WITH SURFACE S1 TO WITHIN 5 arcsec
3. COATING (APPLY ACROSS COATING APERTURE)  
ENVIRONMENTAL DURABILITY:  
PHYSICAL DURABILITY:  
PERFORMANCE SPECIFICATIONS:  
T(avg): >85% FROM 780 - 1600nm FOR RANDOM POLARIZATION @ 45° AOI  
T(abs): >80% FROM 780 - 1600nm FOR ALL POLARIZATIONS @ 45° AOI  
R(avg): >97% FROM 565 - 715nm FOR RANDOM POLARIZATION @ 45° AOI  
R(abs): >95% FROM 565 - 715nm FOR ALL POLARIZATIONS @ 45° AOI  
T(abs): = 50% 750nm @ 45° AOI

S1: HARD COATED  
S2: SINGLE LAYER MgF2



4. FINE GRIND SURFACE

5. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS  
APPLY ACROSS CLEAR APERTURE
6. TRANSMITTED WAVEFRONT DISTORTION RMS@ 632.8nm  $\leq \frac{1}{4} \lambda$
7. ROHS COMPLIANT



LONGPASS FILTER

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	60-40	60-40
CLEAR APERTURE	22.0 x 32.0	22.0 x 32.0
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

**Edmund Optics®**



ALL DIMS IN

mm

TITLE

25.2 x 35.6mm, 750nm DICHROIC LONGPASS  
FILTER

DWG NO

69904

SHEET  
1 OF 1