

NOTES:


1. SUBSTRATE  
CORNING: FUSED SILICA 458/678
2. ROHS COMPLIANT
3. WAVELENGTH RANGE: 200 - 2200nm
4. COATING (APPLY ACROSS COATING APERTURE)  
S1 & S2: UNCOATED

5. FINE GRIND SURFACE

6. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS APPLY ACROSS CLEAR APERTURE

7. IMAGE ORIENTATION: BEAM DEVIATION

8. APPLY ARROW ON EDGE WITH PENCIL OR PERMANENT INK POINTING TOWARDS TILTED SURFACE S2




**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	20 - 10	20 - 10
MIN CLEAR APERTURE	Ø 11.25	Ø 11.25
MIN COATING APERTURE	N/A	N/A
POWER AT 632.8nm	0.5 RINGS	0.5 RINGS
IRREGULARITY AT 632.8nm	0.2 RING	0.2 RING
BEVEL	PROTECTIVE, AS NEEDED	PROTECTIVE, AS NEEDED

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**EO**® Edmund Optics®

THIRD ANGLE  
PROJECTION



TITLE

12.5mm DIA. 2° NOM. FUSED SILICA  
WEDGE PRISM UNCOATED

DWG NO

35845

SHEET  
1 OF 1

ALL DIMS IN

mm