NOTES:

- SUBSTRATE: GRADE A FINE ANNEALED 1. SCHOTT: N-BK7 517/642
- 2. **ROHS COMPLIANT**
- 3. SURFACE \$2 TO BE PARALLEL TO SURFACE \$1 TO WITHIN 3 ARCMIN
- COATING (APPLY ACROSS COATING APERTURE) SPECIFICATIONS AT 45° AOI AND RANDOM POLARIZATION 4.

 $R(abs) = 70\% \pm 5\% @ 550nm$

 $R(abs) = 70\% \pm 10\% FROM 400-700nm$

 $T(abs) = 30\% \pm 5\% @ 550nm$

 $T(abs) = 30\% \pm 10\%$ FROM 400-700nm

VISUÁL COLOR = NEUTRAL

S2: BBAR


R(abs) ≤ 2.0% FROM 400-700nm R(avg) ≤ 1.0% FROM 400-700nm

/5.\

FINE GRIND SURFACE



MARK IDENTIFIES BEAMSPLITTER SURFACE



PARTS TO THIS DRAWING

	\$1	\$2			
SHAPE	PLANO PLANO				
SURFACE FLATNESS	2λ PER mm 2λ PER mm				
SURFACE QUALITY	60 - 40 60 - 40				
MIN CLEAR APERTURE	Ø21.25 Ø21.25				
MIN COATING APERTURE	Ø21.25 Ø21.25				
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED			

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	Edmund Optics ®				
THIRD ANGLE PROJECTION - TITLE BS VIS 70R/30T 25mm DIA 1MM THK					
ALL DIMS IN	mm	DWG NO	35951	SHEET 1 OF 1	