NOTES:

- 1. SUBSTRATE: GRADE A FINE ANNEALED SCHOTT: N-BK7 517/642
- 2. ROHS COMPLIANT
- 3. SURFACE \$2 TO BE PARALLEL TO SURFACE \$1 TO WITHIN 3 ARCMIN
- 4. COATING (APPLY ACROSS COATING APERTURE)
 SPECIFICATIONS AT 45° AOI AND RANDOM POLARIZATION
 S1.

R(abs) = 50% ±5% @ 550nm R(abs) = 50% ±10% FROM 400-700nm

 $T(abs) = 50\% \pm 5\% @ 550$ nm $T(abs) = 50\% \pm 10\%$ FROM 400-700nm

VISUÁL COLOR = NEUTRAL

S2: BBAR


R(abs) ≤ 2.0% FROM 400-700nm R(avg) ≤ 1.0% FROM 400-700nm



FINE GRIND SURFACE



MARK IDENTIFIES BEAMSPLITTER SURFACE



FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

	\$1	\$2			
SHAPE	PLANO PLANO				
SURFACE FLATNESS	2λ PER mm	2λ PER mm			
SURFACE QUALITY	60 - 40	60 - 40			
MIN CLEAR APERTURE	Ø21.25	Ø21.25			
MIN COATING APERTURE	Ø21.25	Ø21.25			
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED			

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

		E	Edmund Optics ®		
THIRD ANG PROJECTIO		TITLE	BS VIS 50R/50T 25mm DIA 1MM THK		
all DIMS IN	mm	DWG NO	35942	SHEET 1 OF 1	