NOTES:

- SUBSTRATE: GRADE A FINE ANNEALED 1. SCHOTT: N-BK7 517/642
- 2. **ROHS COMPLIANT**
- 3. SURFACE \$2 TO BE PARALLEL TO SURFACE \$1 TO WITHIN 3 ARCMIN
- COATING (APPLY ACROSS COATING APERTURE) SPECIFICATIONS AT 45° AOI AND RANDOM POLARIZATION 4.

 $R(abs) = 70\% \pm 5\% @ 550nm$

 $R(abs) = 70\% \pm 10\%$ FROM 400-700nm

 $T(abs) = 30\% \pm 5\% @ 550nm$

 $T(abs) = 30\% \pm 10\%$ FROM 400-700nm

VISUÁL COLOR = NEUTRAL

S2: BBAR


R(abs) ≤ 2.0% FROM 400-700nm R(avg) ≤ 1.0% FROM 400-700nm




FINE GRIND SURFACE



MARK IDENTIFIES BEAMSPLITTER SURFACE





PARTS TO THIS DRAWING

	\$1	\$2	
SHAPE	PLANO	PLANO	
SURFACE FLATNESS	1λ PER 25mm	1λ PER 25mm	
SURFACE QUALITY	60 - 40	60 - 40	
MIN CLEAR APERTURE	42.50 x 63.75	42.50 x 63.75	
MIN COATING APERTURE	42.50 x 63.75	42.50 x 63.75	
BEVEL	PROTECTIVE AS NEEDED PROTECTIVE AS N		

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

		E	Edmund Optics ®		
THIRD ANG PROJECTIO		TITLE	BS VIS 70R/30T 50X75MM 1MM THK		
ALL DIMS IN	mm	DWG NO	35956	SHEET 1 OF 1	