


- NOTES:
- 1. SUBSTRATE:
N-BK7
 - 2. SURFACE S2 TO BE PARALLEL WITH SURFACE S1 TO WITHIN ≤ 3 ARCMIN
 - 3. COATING (APPLY ACROSS CLEAR APERTURE)

S1: 30% R $\pm 5\%$ @ 900nm
70% T $\pm 5\%$ @ 900nm



S2: AR R(avg) $\leq 1\%$, R(abs) $\leq 2\%$ @ 700 - 1100nm

4. CUT WITH 0.25mm MAXIMUM EDGE CHIP
5. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	 Edmund Optics®			
SHAPE	PLANO	PLANO		TITLE	35 x 35mm 30R/70T, NIR Plate Beamsplitter	
ANGLE OF INCIDENCE	45°	45°				
SURFACE QUALITY	60 - 40	60 - 40				
SURFACE FLATNESS	1λ PER 25mm	1λ PER 25mm		DWG NO	49753	SHEET 16 OF 49
			ALL DIMS IN	mm		