### NOTES:

## 1. SUBSTRATE MATERIAL: N-BK7

## 2. ROHS COMPLIANT


3. SURFACE S1 IS PARALLEL TO SURFACE S2 WITHIN ≤ 3 ARCMIN

### 4. COATING (APPLY ACROSS CLEAR APERTURE)

S1: 80% R ±5% @ 550nm 20% T ±5% @ 550nm

S2: AR R(avg) ≤1%, R(abs) ≤2% @ 700 - 1100nm

5. CUT WITH 0.25mm MAXIMUM EDGE CHIP



# FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	\$2				Edmund Optic	<b>CS</b> <sup>®</sup>
SHAPE	PLANO	PLANO					
ANGLE OF INCIDENCE	45°	45°	THIRD ANGLE . PROJECTION			25 x 38mm, 80 R/20 T, PLATE BEAMSPLITTER	
SURFACE QUALITY	60-40	60-40		 			0.1557
SURFACE FLATNESS	1λ PER 25mm	1λ PER 25mm	ALL DIMS IN	mm	DWG NO	68426	SHEET 1 OF 1