NOTES:

1. SUBSTRATE SAPPHIRE (AI2O3)

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

- 2. SURFACE S2 TO BE PARALLEL WITH SURFACE S1 TO WITHIN ≤3.5 ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE)


\$1: R(AVG) ≤ 0.5% FROM 600-1050nm @ 0° AOI


S2: R(AVG) ≤ 0.5% FROM 600-1050nm @ 0° AOI



 POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS APPLY ACROSS CLEAR APERTURE

5. ROHS COMPLIANT





	\$1	\$2	
SHAPE	PLANO	PLANO	
CLEAR APERTURE	Ø18	Ø18	
SURFACE FLATNESS	2λ	2λ	
SURFACE ROUGHNESS	0.1 MICRONS PER INCH	0.1 MICRONS PER INCH	
SURFACE QUALITY	80-50	80-50	
BIREFRINGENCE (n _o -n _e)	0.008	0.008	
BEVEL	PROTECTIVE AS NEEDED	ECTIVE AS NEEDED PROTECTIVE AS NEEDED	

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

			Edmund Optics®		
THIRD ANGLE PROJECTION		TITLE	20mm DIAMETER, NIR I COATED SAPPHIRE WINDOW		
ALL DIMS IN	mm	DWG NO	36498	SHEET 1 OF 1	