## NOTES:

- 1. SUBSTRATE MATERIAL: N-BK7
- 2. ROHS COMPLIANT

 COATING (APPLY ACROSS CLEAR APERTURE) SURFACE MARKED G: NONE SURFACE MARKED S1, S2, S4 & S5:

R(avg) <0.25% @ 632nm @ 0° AOI

SURFACE MARKED S3:

NON-POLARIZING COATING PER FINISHED CUBE


SPECIFICATIONS LISTED BELOW

4. APPLY MARK IDENTIFYING BEAMSPLITTER COATED RIGHT ANGLE PRISM WITH PENCIL OR PERMANENT INK

5. TOLERANCES:

\$1 & \$2 BEAM DEVIATION TO BE WITHIN 2 arcmin \$4 & \$5 BEAM DEVIATION TO BE WITHIN 2 arcmin





## FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

AVERAGE TRANSMISSION	45% ± 5% <3%	
Ts - Tp		
ABSOLUTE TRANSMISSION	45% ± 10%	
SURFACE FLATNESS	λ/8	
SURFACE QUALITY	40-20	
CLEAR APERTURE	90 %	

-			Edmund Optics®		
THIRD ANGLE PROJECTION		TITLE	5mm, 632nm, NON-POLARIZING CUBE BEAMSPLITTER		
ALL DIMS IN	mm	DWG NO	35961	SHEET 1 OF 1	