




NOTES:

- 1. SUBSTRATE:
Fused Silica (Corning 7980)
- 2. TEMPERATURE RANGE:
-40 TO +170 °C


**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SECTION A-A

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1
SPECTRAL RANGE	200 - 1500nm
CLEAR APERTURE	Ø45.7 ± 0.1
DIFFUSING ANGLE	0.5 ±5°
TRANSMISSION EFFICIENCY	90%

 Edmund Optics®			
THIRD ANGLE PROJECTION 		TITLE	50° DIFFUSING ANGLE 50mm DIA., UV HOLOGRAPHIC DIFFUSER
ALL DIMS IN	mm	DWG NO	48522
			SHEET 1 OF 1