

NOTES:




1. SUBSTRATE MATERIAL:
CALCIUM FLUORIDE (CAF₂)
2. COATING (APPLY ACROSS CLEAR APERTURE)

S1:
50/50 ± 20% @ 800 - 2500nm
25/75 ± 15% @ 2500 - 6000nm

S2: NONE

3. RoHS COMPLIANT

 4. GROUND SURFACE



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	60-40	60-40
SURFACE FLATNESS	3λ/4	3λ/4
CLEAR APERTURE	Ø22.50	Ø22.50



ALL DIMS IN mm

 **Edmund Optics®**

TITLE

25mm Diameter, 0.8-6µm Calcium Fluoride IR
Plate Beamsplitter

DWG NO

36656

SHEET
1 OF 1