

NOTES:

1. SUBSTRATE MATERIAL:
N-SF5
2. COATING (APPLY ACROSS CLEAR APERTURE)


S1: PROTECTED GOLD
R(avg) >89% @ 250 - 450nm
R(avg) >94% @ 700 - 800nm

S2: NONE

3. POWER, IRREGULARITY, SURFACE QUALITY, AND COATING
SPECIFICATIONS APPLY ACROSS CLEAR APERTURE



 FINE GROUND SURFACE

5. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2	<div>DIMENSIONS ARE FOR REFERENCE ONLY</div> <div><div> Edmund Optics®</div></div>				
SHAPE	CONVEX	PLANO					
RADIUS	51.68	INFINITY					
EFFECTIVE FOCAL LENGTH	-25.8mm	N/A					
FOCAL LENGTH TOLERANCE	±2%	N/A					
SURFACE QUALITY	60-40	COMMERCIAL POLISH	<div>THIRD ANGLE PROJECTION</div> 	TITLE	Ø25mm, -25.8mm FL PROTECTED GOLD, CONVEX SPHERICAL MIRROR		
CLEAR APERTURE	90%	N/A		ALL DIMS IN	mm	DWG NO	64076
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED					