


- NOTES:
- 1. COATING (APPLY ACROSS CLEAR APERTURE)
LASER V-COAT
R(ABS) ≤ 0.25% @ 1064nm
 - 2. RoHS: COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

DAMAGE THRESHOLD (PULSED)	10J/cm ² @ 10ns, 20Hz, 1064nm
DESIGN WAVELENGTH DWL (nm)	1064
EXPANSION POWER	5X
TRANSMISSION (%)	> 99 (NOMINAL)
NOMINAL PERFORMANCE	<λ/10 FOR 4mm INPUT BEAM (NOMINAL)

THIRD ANGLE
PROJECTION

ALL DIMS IN mm

Edmund Optics®			
TITLE	5X 1064nm VEGA™ Nd:YAG LASER LINE BEAM EXPANDER		
DWG NO	35103	SHEET 1 OF 1	