

NOTES:

1. SUBSTRATE MATERIAL:  
N-BK7

2. COATING (APPLY ACROSS CLEAR APERTURE)


S1 & S2:  
LASER V-COAT

R(abs) <0.25% @ 1064nm

3. FINE GROUND SURFACE


4. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS APPLY ACROSS CLEAR APERTURE

5. RoHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2					
SHAPE	CONVEX	PLANO	EFL	75±3%	 <b>Edmund Optics®</b>		
RADIUS	38.89	∞	BFL	(72.89)			
SURFACE QUALITY	60-40	60-40	THIRD ANGLE PROJECTION 		TITLE	25.0mm DIA X 75.0mm FL 1064nm V-COAT, CYLINDER LENS	
CLEAR APERTURE	∅ 24.00	∅ 24.00			ALL DIMS IN	mm	DWG NO
COATING APERTURE	∅ 24.00	∅ 24.00					SHEET 1 OF 1
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED					