


NOTES:

- 1. SUBSTRATE MATERIAL:
N-BK7
- 2. COATING (APPLY ACROSS CLEAR APERTURE)

S1 & S2: VIS 0°



R(avg) ≤0.4% @ 425 - 675nm

- 3. FINE GROUND SURFACE
- 4. POWER, IRREGULARITY, AND SURFACE QUALITY
SPECIFICAIONS APPLY ACROSS CLEAR APERTURE
- 5. RoHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

| | | | | | | |
|------------------|---------------------|---------------------|---|--------|--|---|
| REV. A | S1 | S2 | | | | |
| SHAPE | CONVEX | PLANO | EFL | -50 |  Edmund Optics® | |
| RADIUS | -25.93 | ∞ | BFL | -51.97 | | |
| SURFACE QUALITY | 60-40 | 60-40 |  | | TITLE | 25mm DIA X -50mm FL VIS 0° COATED, CYLINDER LENS |
| CLEAR APERTURE | Ø24.00 | Ø24.00 | | | DWG NO | 69803 |
| COATING APERTURE | Ø24.00 | Ø24.00 | | | | |
| BEVEL | PROTECTED AS NEEDED | PROTECTED AS NEEDED | | | | |
| | | | ALL DIMS IN | mm | SHEET 1 OF 1 | |