

NOTES:

1. SUBSTRATE MATERIAL:
N-BK7
2. COATING (APPLY ACROSS CLEAR APERTURE)



S1 & S2: VIS-NIR

R(abs) $\leq 0.25\%$ @ 880nm
R(ave) $\leq 1.25\%$ @ 400 - 870nm
R(ave) $\leq 1.25\%$ @ 890 - 1000nm


3. FINE GROUND SURFACE

4. POWER, IRREGULARITY, AND SURFACE QUALITY
SPECIFICATIONS APPLY ACROSS CLEAR APERTURE
5. RoHS COMPLIANT

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2	<div><div><div>EFL</div><div>-100</div></div><div><div>BFL</div><div>-102.64</div></div></div> <div><div><div><div></div><div></div></div><div></div></div><div>Edmund Optics®</div></div>				
SHAPE	CONVEX	PLANO					
RADIUS	51.68	∞					
SURFACE QUALITY	60-40	60-40					
CLEAR APERTURE	24.00 X 49.00	24.00 X 49.00					
COATING APERTURE	24.00 X 49.00	24.00 X 49.00					
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED	THIRD ANGLE PROJECTION		TITLE	25mm H X 50mm L X -100mm FL VIS-NIR COATED, CYLINDER LENS	
			ALL DIMS IN	mm	DWG NO	69849	SHEET 1 OF 1